

**Garant****Indexable insert for turning DC.T 11T302, for medium machining, Grade: HB7310****Order data**

Order number	260458 HB7310
GTIN	4045197669568
Item class	21G

**Technical description**

Feed f	0.05 - 0.5 mm/rev.
Cutting speed $v_c$ main application	350 - 600 m/min
Cutting depth $a_p$	0.1 - 4 mm
Cutting conditions	continuous
Chip breaker	AM
Corner radius	0.2 mm
Main application	N
Grade	HB7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DCGT 11T302
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning