

**Garant**
**Clamping toolholder MVJNR 93°, for indexable inserts VN., right-hand,  
Shank / insert size: 25/16mm**

**Order data**

Order number	251706 25/16
GTIN	4045197651020
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	32 mm
suitable indexable insert	VN.. 1604..
Insert size	16 mm
Screw for clamping claw	259021 1
ISO code toolholder	MVJNR/L 2525M16
Shim	259031 39
Clamping claw	259038 2
Shank size	25 mm
Shim screw	259025 3
Head length L <sub>1</sub>	32 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Screw for clamping claw Type 1	259021 1
Shim screw Type 3	259025 3
Shim Type 39	259031 39
Clamping claw Type 2	259038 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8