

Garant

Indexable insert for turning DC.T 11T304, for medium machining, Grade: HU7310

**Order data**

Order number	260462 HU7310
GTIN	4045197669766
Item class	21G

Technical description

Cutting conditions	continuous
Chip breaker	AM
Cutting speed v_c main application	350 - 600 m/min
Corner radius	0.4 mm
Main application	N
Cutting depth a_p	0.1 - 4 mm
Feed f	0.05 - 0.5 mm/rev.
Grade	HU7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

Coating	uncoated
ISO code indexable insert	DCGT 11T304
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning