

**Garant**

**Indexable insert for turning DC.T 11T308, for medium machining, Grade: HU7310**

**Order data**

Order number	260464 HU7310
GTIN	4045197669940
Item class	21G

**Technical description**

Cutting depth $a_p$	0.1 - 4 mm
Feed $f$	0.05 - 0.5 mm/rev.
Chip breaker	AM
Cutting speed $v_c$ main application	350 - 600 m/min
Corner radius	0.8 mm
Cutting conditions	continuous
Main application	N
Grade	HU7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

Coating	uncoated
ISO code indexable insert	DCGT 11T308
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning