

**Garant**
**Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 16/10mm**

**Order data**

Order number	260607 16/10
GTIN	4045197655387
Item class	21T

**Technical description**

Head length $L_1$	15.5 mm
Functional width $L_4$	20 mm
Insert size	10 mm
Shank size	16 mm
ISO code toolholder	SRGCR/L 1616H10
suitable indexable insert	RC.T 1003
Shim	269005 11
Shim screw	269013 2
Pack of insert screws	269028 2
Overall length $L$	100 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 11	269005 11
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8