

**Garant**

**Carbide boring bar E.. SGLPL 95°, for indexable inserts GPCT, left-hand,  
Overhang / insert size: 100/06mm**


**Order data**

Order number	268736 100/06
GTIN	4045197545909
Item class	21V

**Technical description**

ISO code toolholder	E12M SGLCR/L06
Insert size	6 mm
Pack of insert screws	269028 11
Centre offset $L_3$	9.15 mm
Minimum pre-drill $\varnothing D_{min}$	15.52 mm
suitable indexable insert	GCCT 06020.
Overall length L	150 mm
Clamping height $L_2$	11.33 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Set of insert screws Type 11	269028 11
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7