

Garant

**Carbide boring bar E.. STLDL 95°, for indexable inserts TDAT, left-hand,
Overhang / insert size: 85/07mm**


Order data

Order number	268826 85/07
GTIN	4045197562678
Item class	21V

Technical description

Insert size	7 mm
Centre offset L_3	4.8 mm
ISO code toolholder	E08K STLDR/L07
Minimum pre-drill $\varnothing D_{\min}$	9.14 mm
Pack of insert screws	269028 12
suitable indexable insert	TDAT 07010.
Overall length L	125 mm
Clamping height L_2	7.49 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 12	269028 12
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6