

Garant
**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 16/12mm**

Order data

Order number	250018 16/12
GTIN	4045197649942
Item class	21T

Technical description

Lever	259015 2
ISO code toolholder	PCLNR/L 1616H12
Insert size	12 mm
Shank size	16 mm
Shim	259031 2
Functional width L ₄	20 mm
Shim pins pack	259044 2
Lever screw	259018 8
Head length L ₁	25 mm
Shim punches pack	259047 2
suitable indexable insert	CN.. 1204..
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 8	259018 8
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2