

**Garant**
**Carbide boring bar E.. STFCL 90°, for indexable inserts TC., left-hand, Shank Ø / insert size: 12/11mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 260919 12/11  |
| GTIN         | 4045197653406 |
| Item class   | 21T           |

**Technical description**

|   |                |
|---|----------------|
| ISO code toolholder                     | E12M STFCL/L11 |
| suitable indexable insert               | TC.. 1102..    |
| Centre offset $L_3$                     | 8 mm           |
| Minimum pre-drill $\varnothing D_{min}$ | 15 mm          |
| Insert size                             | 11 mm          |
| Head length $L_1$                       | 20 mm          |
| Pack of insert screws                   | 269028 7       |
| Overall length L                        | 150 mm         |
| Clamping height $L_2$                   | 11.5 mm        |
| Setting angle $\kappa$                  | 90 degrees     |
| Shank $\varnothing D_s$                 | 12 mm          |
| Standard                                | Works standard |
| Application type                        | left-hand      |
| Boring depth up to                      | 8xD            |
| Tool material                           | Carbide        |
| Through-coolant                         | yes            |

|                 |                               |
|-----------------|-------------------------------|
| Application     | Internal longitudinal turning |
| Type of product | Boring Bar                    |

---

## Accessories

|  |            |
|--|------------|
| Set of insert screws Type 7  | 269028 7   |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8                             | 674248 TX8 |