

**Garant**

**Clamping toolholder DCLNR 95°, for indexable inserts CN., right-hand,  
Shank / insert size: 25/12mm**



### Order data

Order number	250016 25/12
GTIN	4045197649881
Item class	21T

### Technical description

Shim	259031 2
Shim screw	259025 10
Clamp, screw, spring	259035 2
Head length L <sub>1</sub>	33 mm
Insert size	12 mm
Functional width L <sub>4</sub>	32 mm
ISO code toolholder	DCLNR/L 2525M12
suitable indexable insert	CN.. 1204..
Shank size	25 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw Type 10	259025 10
Shim Type 2	259031 2
Clamp unit Type 2	259035 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20