

Garant
Clamping toolholder PCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 32/19mm

Order data

Order number	250019 32/19
GTIN	4045197650047
Item class	21T

Technical description

Head length L ₁	40 mm
Shim pins pack	259044 7
Lever screw	259018 13
Lever	259015 13
Insert size	19 mm
ISO code toolholder	PCLNR/L 3232P19
suitable indexable insert	CN.. 1906..
Shank size	32 mm
Functional width L ₄	40 mm
Shim punches pack	259047 5
Shim	259031 36
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 13	259015 13
Lever screw Type 13	259018 13
Shim Type 36	259031 36
Set of shim pins 10 pieces Type 7	259044 7