

Garant**Indexable insert for turning SC.T 120404, for medium machining, Grade: HU7310****Order data**

Order number	260765 HU7310
GTIN	4045197670502
Item class	21G

Technical description

Chip breaker	AM
Corner radius	0.4 mm
Feed f	0.05 - 0.5 mm/rev.
Cutting depth a_p	0.1 - 4 mm
Cutting conditions	continuous
Main application	N
Grade	HU7310
Cutting speed v_c main application	350 - 600 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated

ISO code indexable insert	SCGT 120404
Number of changes/inserts	4
Tolerance	G
Type of product	Indexable insert for turning