

Garant

Carbide boring bar E.. STFCR 90°, for indexable inserts TC., right-hand, Shank Ø / insert size: 10/11mm


Order data

| | |
|--------------|---------------|
| Order number | 260918 10/11 |
| GTIN | 4045197653369 |
| Item class | 21T |

Technical description

| | |
|-------------------------------|----------------|
| Minimum pre-drill Ø D_{min} | 12 mm |
| Pack of insert screws | 269028 7 |
| ISO code toolholder | E10K STFCR/L11 |
| suitable indexable insert | TC.. 1102.. |
| Centre offset L_3 | 6 mm |
| Head length L_1 | 16 mm |
| Insert size | 11 mm |
| Overall length L | 125 mm |
| Clamping height L_2 | 9.6 mm |
| Setting angle κ | 90 degrees |
| Shank Ø D_s | 10 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 8×D |
| Tool material | Carbide |
| Through-coolant | yes |

| | |
|-----------------|-------------------------------|
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |

Accessories

| | |
|--|------------|
| Set of insert screws Type 7 | 269028 7 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |