

Garant
Clamping toolholder SCLCR 95°, for indexable inserts CC., right-hand, Shank / insert size: 12/09mm

Order data

Order number	260006 12/09
GTIN	4045197654830
Item class	21T

Technical description

Shank size	12 mm
Functional width L ₄	16 mm
suitable indexable insert	CC.. 09T3..
Head length L ₁	13 mm
Pack of insert screws	269028 2
Insert size	9 mm
ISO code toolholder	SCLCR/L 1212F09
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15