

Garant

Carbide boring bar E.. STFCR 90°, for indexable inserts TC., right-hand, Shank Ø / insert size: 12/11mm


Order data

Order number	260918 12/11
GTIN	4045197653376
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	15 mm
ISO code toolholder	E12M STFCR/L11
Centre offset L_3	8 mm
Head length L_1	20 mm
Insert size	11 mm
Pack of insert screws	269028 7
suitable indexable insert	TC.. 1102..
Overall length L	150 mm
Clamping height L_2	11.5 mm
Setting angle κ	90 degrees
Shank Ø D_s	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8