

Garant

Clamping toolholder SCLCR 95°, for indexable inserts CC., right-hand, Shank / insert size: 16/09mm



Order data

Order number	260006 16/09
GTIN	4045197651624
Item class	21T

Technical description

suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Head length L ₁	17 mm
Pack of insert screws	269028 2
Shim	269005 1
Shim screw	269013 2
Functional width L ₄	20 mm
ISO code toolholder	SCLCR/L 1616H09
Shank size	16 mm
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 1	269005 1
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15