

**Garant**

**Carbide boring bar E.. STFCL 90°, for indexable inserts TC., left-hand, Shank Ø / insert size: 10/11mm**


**Order data**

Order number	260919 10/11
GTIN	4045197653390
Item class	21T

**Technical description**

Pack of insert screws	269028 7
ISO code toolholder	E10K STFCL/L11
suitable indexable insert	TC.. 1102..
Head length $L_1$	16 mm
Centre offset $L_3$	6 mm
Minimum pre-drill Ø $D_{min}$	12 mm
Insert size	11 mm
Overall length L	125 mm
Clamping height $L_2$	9.6 mm
Setting angle $\kappa$	90 degrees
Shank Ø $D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8