

Garant

Clamping toolholder SCLCR 95°, for indexable inserts CC., right-hand, Shank / insert size: 25/09mm



Order data

Order number	260006 25/09
GTIN	4045197651648
Item class	21T

Technical description

Shank size	25 mm
Functional width L ₄	32 mm
suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Shim screw	269013 2
Shim	269005 1
Pack of insert screws	269028 2
ISO code toolholder	SCLCR/L 2525M09
Head length L ₁	19 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 1	269005 1
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15