



Side lock arbor Form AD, SK 30 short, Clamping range $\varnothing D_1$: 10mm



Order data

Order number	300050 10
GTIN	4045197674319
Item class	32A

Description

Version:

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Spare clamping screw No. 30 9900	10
Clamping $\varnothing D_1$	10 mm
Overhang dimension A	50 mm
External $\varnothing D$	35 mm
Adapter	SK 30 short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm

Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud 45°sealed suitable for steep tapers 30	308760 30
Pull stud 60°sealed suitable for steep tapers 30	308785 30
Pull studsealed, form A suitable for steep tapers 30	308610 30
Pull stud 45°sealed suitable for steep tapers 30	308765 30
Spare clamping screw for chucks with clamping Ø D1 10 mm	309900 10