

**Garant**

**Carbide boring bar E.. SCLCL 95°, for indexable inserts CC.., left-hand, Shank Ø / insert size: 12/06mm**


**Order data**

Order number	260017 12/06
GTIN	4045197651907
Item class	21T

**Technical description**

Centre offset $L_3$	8 mm
Insert size	6 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Pack of insert screws	269028 7
suitable indexable insert	CC.. 0602..
Head length $L_1$	10 mm
ISO code toolholder	E12M SCLCR/L06
Overall length $L$	150 mm
Clamping height $L_2$	11.5 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	12 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8