

Garant

Indexable insert for turning VB.T 160404, for medium machining, Grade: HB7310

**Order data**

Order number	261232 HB7310
GTIN	4045197696267
Item class	21G

Technical description

Main application	N
Cutting conditions	continuous
Feed f	0.05 - 0.5 mm/rev.
Cutting speed v_c main application	350 - 600 m/min
Corner radius	0.4 mm
Chip breaker	AM
Cutting depth a_p	0.1 - 4 mm
Grade	HB7310
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide

ISO code indexable insert	VBGT 160404
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning