

**Garant**

**Clamping toolholder SVJCL 93°, for indexable inserts VC., left-hand, Shank / insert size: 12/11mm**



### Order data

Order number	261313 12/11
GTIN	4045197655950
Item class	21T

### Technical description

Insert size	11 mm
Head length L <sub>1</sub>	21.5 mm
Pack of insert screws	269028 22
Functional width L <sub>4</sub>	16 mm
suitable indexable insert	VC.. 1103..
Shank size	12 mm
ISO code toolholder	SVJCR/L 1212F11
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8