

Garant

Steel boring bar A.. SCLCL 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 20/09mm


Order data

Order number	260032 20/09
GTIN	4045197652263
Item class	21T

Technical description

ISO code toolholder	A20R SCLCR/L09
Insert size	9 mm
suitable indexable insert	CC.. 09T3..
Pack of insert screws	269028 8
Minimum pre-drill Ø D_{min}	25 mm
Centre offset L_3	13 mm
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	95 degrees
Shank Ø D_s	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15