

Garant

Clamping toolholder SVJCL 93°, for indexable inserts VC., left-hand, Shank / insert size: 25/11mm



Order data

Order number	261313 25/11
GTIN	4045197655967
Item class	21T

Technical description

Functional width L_4	32 mm
ISO code toolholder	SVJCR/L 2525M11
suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 22
Shank size	25 mm
Head length L_1	26 mm
Insert size	11 mm
Overall length L	150 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8