

**Garant**

**Clamping toolholder SVJCR 93°, for indexable inserts VC., right-hand, Shank / insert size: 20/11mm**



### Order data

Order number	261312 20/11
GTIN	4045197653826
Item class	21T

### Technical description

Pack of insert screws	269028 22
Shank size	20 mm
Head length L <sub>1</sub>	24 mm
Insert size	11 mm
ISO code toolholder	SVJCR/L 2020K11
suitable indexable insert	VC.. 1103..
Functional width L <sub>4</sub>	25 mm
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8