

**Garant**

**Carbide boring bar E.. STLDL 95°, for indexable inserts TDAT, left-hand,  
Overhang / insert size: 75/07mm**


**Order data**

Order number	268826 75/07
GTIN	4045197562661
Item class	21V

**Technical description**

Pack of insert screws	269028 12
Centre offset $L_3$	3.71 mm
ISO code toolholder	E06J STLDL/L07
suitable indexable insert	TDAT 07010.
Insert size	7 mm
Minimum pre-drill $\varnothing D_{min}$	7.06 mm
Overall length L	110 mm
Clamping height $L_2$	5.54 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 12	269028 12
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6