

Garant

**Carbide boring bar E.. SGLPR 95°, for indexable inserts GPCT, right-hand,
Overhang / insert size: 75/S5mm**


Order data

Order number	268732 75/S5
GTIN	4045197545831
Item class	21V

Technical description

Insert size	5 mm
ISO code toolholder	E06J SGLPR/LS5
suitable indexable insert	GPCT S5010.
Pack of insert screws	269028 6
Centre offset L_3	5.6 mm
Minimum pre-drill $\varnothing D_{\min}$	9.15 mm
Overall length L	110 mm
Clamping height L_2	5.54 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 6	269028 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6