

Garant

Steel boring bar A.. SVJCL 142°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	261339 20/11
GTIN	4045197654113
Item class	21T

Technical description

Minimum pre-drill Ø D _{min}	24 mm
Head length L ₁	38 mm
ISO code toolholder	A20Q SVJCR/L11
Neck width L ₄	11 mm
Insert size	11 mm
Centre offset L ₃	2 mm
Pack of insert screws	269028 7
suitable indexable insert	VC.. 1103..
Overall length L	180 mm
Clamping height L ₂	19 mm
Setting angle κ	142 degrees
Shank Ø D _s	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8