

Garant

Indexable insert for turning VCGT 110302, for medium machining, Grade: HU7310

**Order data**

Order number	261453 HU7310
GTIN	4045197671561
Item class	21G

Technical description

Cutting depth a_p	0.1 - 4 mm
Cutting conditions	continuous
Feed f	0.05 - 0.5 mm/rev.
Corner radius	0.2 mm
Cutting speed v_c main application	350 - 600 m/min
Chip breaker	AM
Main application	N
Grade	HU7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	VCGT 110302
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning