

Garant

**Carbide boring bar E.. STLDR 95°, for indexable inserts TDAT, right-hand,
Overhang / insert size: 85/07mm**


Order data

Order number	268822 85/07
GTIN	4045197562654
Item class	21V

Technical description

Centre offset L_3	4.8 mm
suitable indexable insert	TDAT 07010.
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	9.14 mm
Pack of insert screws	269028 12
ISO code toolholder	E08K STLDR/L07
Overall length L	125 mm
Clamping height L_2	7.49 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 12	269028 12
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6