

Garant

Carbide boring bar E.. STFCL 90°, for indexable inserts TC., left-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	260919 16/11
GTIN	4045197653413
Item class	21T

Technical description

Insert size	11 mm
ISO code toolholder	E16R STFCL/L11
Minimum pre-drill Ø D_{min}	19 mm
Pack of insert screws	269028 7
Head length L_1	25 mm
suitable indexable insert	TC.. 1102..
Centre offset L_3	10 mm
Overall length L	200 mm
Clamping height L_2	15.4 mm
Setting angle κ	90 degrees
Shank Ø D_s	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8