

**Garant****Indexable insert for turning TC.T 16T304, for medium machining, Grade: HU7310****Order data**

Order number	260986 HU7310
GTIN	4045197671127
Item class	21G

**Technical description**

Cutting conditions	continuous
Chip breaker	AM
Feed f	0.05 - 0.5 mm/rev.
Main application	N
Cutting speed $v_c$ main application	350 - 600 m/min
Corner radius	0.4 mm
Cutting depth $a_p$	0.1 - 4 mm
Grade	HU7310
Finishing/roughing assignment	Finishing
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	TCGT 16T304

Number of changes/inserts	3
Tolerance	G
Type of product	Indexable insert for turning