

Garant

**Clamping toolholder SVHCL 107,5°, for indexable inserts VC., left-hand,
Shank / insert size: 16/11mm**



Order data

Order number	261309 16/11
GTIN	4045197655929
Item class	21T

Technical description

Functional width L ₄	20 mm
Shank size	16 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 22
ISO code toolholder	SVHCR/L 1616H11
Head length L ₁	13 mm
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8