

Garant

Clamping toolholder SVJCL 93°, for indexable inserts VC., left-hand, Shank / insert size: 20/11mm



Order data

Order number	261313 20/11
GTIN	4045197653871
Item class	21T

Technical description

Head length L_1	24 mm
Pack of insert screws	269028 22
Functional width L_4	25 mm
suitable indexable insert	VC.. 1103..
Shank size	20 mm
Insert size	11 mm
ISO code toolholder	SVJCR/L 2020K11
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8