

Garant

Clamping toolholder SVJCR 93°, for indexable inserts VC., right-hand, Shank / insert size: 25/11mm



Order data

Order number	261312 25/11
GTIN	4045197653833
Item class	21T

Technical description

ISO code toolholder	SVJCR/L 2525M11
Pack of insert screws	269028 22
Insert size	11 mm
Shank size	25 mm
suitable indexable insert	VC.. 1103..
Functional width L ₄	32 mm
Head length L ₁	26 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8