

Garant

Clamping toolholder SVVCN 72,5°, for indexable inserts VC., neutral, Shank / insert size: 12/11mm



Order data

Order number	261317 12/11
GTIN	4045197655974
Item class	21T

Technical description

ISO code toolholder	SVVCN 1212F11
Pack of insert screws	269028 22
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Overall length L neutral holders	80 mm
Shank size	12 mm
Overhang L ₁ neutral holders	18 mm
Functional width L ₄ neutral holders	6 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8