

**Garant**

**Clamping toolholder SVVCN 72,5°, for indexable inserts VC., neutral, Shank / insert size: 25/11mm**



### Order data

Order number	261317 25/11
GTIN	4045197653925
Item class	21T

### Technical description

Insert size	11 mm
Pack of insert screws	269028 22
ISO code toolholder	SVVCN 2525M11
Overhang L <sub>1</sub> neutral holders	39 mm
Overall length L neutral holders	150 mm
Shank size	25 mm
suitable indexable insert	VC.. 1103..
Functional width L <sub>4</sub> neutral holders	12.5 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8