

Garant

Steel boring bar A.. SVJCR 142°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	261338 20/11
GTIN	4045197654083
Item class	21T

Technical description

suitable indexable insert	VC.. 1103..
ISO code toolholder	A20Q SVJCR/L11
Minimum pre-drill Ø D_{min}	24 mm
Head length L_1	38 mm
Insert size	11 mm
Centre offset L_3	2 mm
Pack of insert screws	269028 7
Neck width L_4	11 mm
Overall length L	180 mm
Clamping height L_2	19 mm
Setting angle κ	142 degrees
Shank Ø D_s	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8