

**Indexable insert for turning DNMA 150604, CBN (0°), Cutting edge version: M****Order data**

Order number	255584 M
GTIN	4045197817648
Item class	22I

Description**Version:**

- Disposable insert.
- Single cutting edge.

Note:

Further indexable insert shapes, sizes and corner radii available on request.

Technical description

Grade	BUX220
Cutting depth a_p	0.1 - 0.5 mm
Cutting edge version	M
Corner radius	0.4 mm
Feed f	0.1 - 0.2 mm/rev.
Cutting conditions	continuous
Cutting speed v_c main application	80 - 200 m/min

Finishing/roughing assignment	Finishing
Tool material	CBN
ISO code indexable insert	DNMA 150604
Number of changes/inserts	1
Product name attribute	BUX220
Type of product	Indexable insert for turning