

Garant

"5 in 1" drilling and turning tool 2.25×D, right-hand, Ø DC: 15mm


Order data

Order number	268467 15
GTIN	4045197470157
Item class	21K

Description
Version:

With internal cooling.

Plain shank **with collar**.

Application:

Face turning, longitudinal turning, drilling, internal longitudinal turning, countersinking.

Note:

- **Choose corner radii as large as possible.**
- **Always use internal cooling for drilling (at least 5 bar).**

Use the drilling and turning tool **in long chipping structural steels and long chipping stainless steels only up to 1.5×D.**

Technical description

Nominal Ø D	15 mm
Shank Ø D _s	20 mm
Indexable insert No. 268472 – 268496	WCHX 0703..
Bore Ø tolerance D	0/+0.27 mm
Pack of insert screws	269028 33
Shank length L _s	50 mm
Reach L ₁	33.75 mm
Ø d ₂	25 mm

Overhang L _A	43 mm
Series	"5 in 1"
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws Type 33	269028 33
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8