

**Garant****Indexable insert for turning VCGT 110301 FN, PKD (7°), Cutting edge version: N****Order data**

Order number	265872 N
GTIN	4045197644275
Item class	21L

**Description****Version:**

**PCD** – Polycrystalline diamond, fine grain. Neutral, without chip breaker.

**Application:**

For aluminium, aluminium alloys, non-ferrous metals, plastics, composite materials, titanium alloys, sintered metals.

**Technical description**

Corner radius	0.1 mm
Cutting depth $a_p$	0.1 - 2.5 mm
Cutting speed $v_c$ for G(C)RP	150 - 600 m/min
Cutting speed $v_c$ for alu < 10 % Si	300 - 2000 m/min
Feed $f$	0.03 - 0.4 mm/rev.
Cutting edge version	N

Cutting speed $v_c$ for non-ferrous metals	300 - 1500 m/min
Cutting conditions	continuous
Grade	PCD
Finishing/roughing assignment	Semi-roughing
Tool material	PCD
ISO code indexable insert	VCGT 110301 FN
Number of changes/inserts	1
Product name attribute	PCD
Rake	6 degrees
Type of product	Indexable insert for turning