

Garant**Short drill chuck Form AD/B, SK 50, Clamping range: 0,5-16mm****Order data**

Order number	301467 0,5-16
GTIN	4045197573414
Item class	31B

Description**Version:**

For clockwise and anticlockwise rotation.

With Balluff/RFID chip bore. Maximum radial run-out $\leq 20 \mu\text{m}$.

Glass bead blasted.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping range	0.5 - 16 mm
Overhang dimension A	106 mm
Type	Standard
Spare chuck key No. 627425	SW 6
External Ø D	57 mm
Adapter	SK 50
Arbor standard	ISO 7388-1
Shape	ADB
Through-coolant	yes, with max. 50 bar

Balance quality G at rotational speed	G 2.5 at 18,000 rpm
Concentricity	≤ 20 µm
maximum tightening torque $M_{d\ max}$	≤ 14 Nm
Type of product	Short drill chuck

Accessories

Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50