

Garant

Indexable insert for turning WCHX 10T304, for "5 in 1" turning and boring tools, Type: SM


Order data

| | |
|--------------|---------------|
| Order number | 268492 SM |
| GTIN | 4045197470904 |
| Item class | 21K |

Description
Suitable for:

Boring tool No. 268463 – 268468, size 20.

Technical description

| | |
|---|-----------------|
| Cutting speed v_c secondary application | 110 - 140 m/min |
| Secondary application | M |
| Cutting speed v_c main application | 110 - 220 m/min |
| Main application | P |
| Corner radius | 0.2 mm |
| Type | SM |
| Grade | HB7120 |
| Tool material | Carbide |
| ISO code indexable insert | WCHX 10T304 |
| Number of changes/inserts | 3 |

suitable for tool dia. D_c

20 mm

Type of product

Indexable insert for turning