

Garant

Indexable insert for turning WCHX 10T308, for "5 in 1" turning and boring tools, Type: ALU

**Order data**

Order number	268494 ALU
GTIN	4045197470942
Item class	21K

Description**Suitable for:**

Boring tool No. 268463 – 268468, size 20.

Technical description

Corner radius	0.2 mm
Cutting speed v_c main application	300 - 600 m/min
Main application	N
Cutting speed v_c secondary application	180 m/min
Type	ALU
Secondary application	K
Grade	HU70AL
Tool material	Carbide
ISO code indexable insert	WCHX 10T308
Number of changes/inserts	3

suitable for tool dia. D_c	20 mm
Type of product	Indexable insert for turning