

Garant
Pull stud, 18CrNiMo7 Form A, with bore, suitable for steep tapers: 50

Order data

Order number	308605 50
GTIN	4045197554536
Item class	31Z

Description
Description:

The toolholder is securely pulled into the spindle by the spindle's clamping gripper using the pull stud. Pull studs come in different versions. They are an important link between the machine and tool. Stringent requirements apply for the accuracy, strength and reliability of pull studs.

Application:

- **For tools with taper shanks see also DIN 69871 and JIS B 6339 (MAS-BT).**
- **In machining centres (machines with automatic tool changers).**
- **In NC machines (machines without automatic tool changers).**

Note:

When installing the pull stud, cheque the correct tightening torque.

ISO 7388-3 meets the old standard DIN 69872.

Technical description

Thread M	M24
Overall length L	74 mm
Angle A	15 degrees
maximum tightening torque	150 Nm
suitable for steep tapers	50
suitable for taper arbors with colour code	SK 50
Head $\varnothing D_1$	28 mm

Collar Ø D	36 mm
L ₁	34 mm
Width across flats	19 mm
Hole characteristics	with bore
Pull stud standard	ISO 7388-3
Type of product	Pull Stud

Accessories

Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308825 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50