


Indexable insert for turning TNMA 160404, CBN (0°), Cutting edge version: M

Order data

Order number	255590 M
GTIN	4045197817679
Item class	22I

Description
Version:

- **Disposable insert.**
- **Single cutting edge.**

Note:

Further indexable insert shapes, sizes and corner radii available on request.

Technical description

Cutting depth a_p	0.1 - 0.5 mm
Feed f	0.1 - 0.2 mm/rev.
Grade	BUX220
Cutting edge version	M
Cutting speed v_c main application	80 - 200 m/min
Corner radius	0.4 mm
Cutting conditions	continuous
Cutting conditions	slightly interrupted

Finishing/roughing assignment	Finishing
Tool material	CBN
ISO code indexable insert	TNMA 160404
Number of changes/inserts	1
Product name attribute	BUX220
Type of product	Indexable insert for turning