



Indexable insert for turning TNMA 160408, CBN (0°), Cutting edge version: M



Order data

Order number	255592 M
GTIN	4045197817686
Item class	22I

Description

Version:

- Disposable insert.
- Single cutting edge.

Note:

Further indexable insert shapes, sizes and corner radii available on request.

Technical description

Feed f	0.1 - 0.2 mm/rev.
Cutting conditions	continuous
Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Cutting edge version	M
Cutting speed v_c main application	80 - 200 m/min
Cutting depth a_p	0.1 - 0.5 mm
Grade	BUX220

Finishing/roughing assignment	Finishing
Tool material	CBN
ISO code indexable insert	TNMA 160408
Number of changes/inserts	1
Product name attribute	BUX220
Type of product	Indexable insert for turning