

Garant
Pull stud sealed, without bore, suitable for steep tapers: 40

Order data

Order number	308660 40
GTIN	4045197151001
Item class	31Z

Description
Description:

The toolholder is securely pulled into the spindle by the spindle's clamping gripper using the pull stud. Pull studs come in different versions. They are an important link between the machine and tool. Stringent requirements apply for the accuracy, strength and reliability of pull studs.

Application:

- **For tools with taper shanks see also DIN 69871 and JIS B 6339 (MAS-BT).**
- **In machining centres (machines with automatic tool changers).**
- **In NC machines (machines without automatic tool changers).**

Note:

Sealed – with O-ring.

Look in the eShop – you will find the right clamping wrench and width for every job.

When installing the pull stud, cheque the correct tightening torque.

Technical description

maximum tightening torque	50 Nm
Head $\varnothing D_1$	18.95 mm
suitable for steep tapers	40
Thread M	M16
suitable for taper arbors with colour code	SK 40
Collar $\varnothing D$	22.5 mm

Overall length L	44.5 mm
L ₁	16.25 mm
Width across flats	18 mm
Hole characteristics	without bore
Pull stud standard	ISO 7388
Type of product	Pull Stud

Accessories

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
---	-----------