

**Straight shank drill chuck arbor, Shank Ø / drill chuck taper: 10/12mm****Order data**

Order number	342300 10/12
GTIN	4045197294906
Item class	32X

Description**Version:**

Through hardened and ground. High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

High precision version with plain shank.

Application:

For mounting drill chucks on to milling machines, automatic system etc. The plain shank can be clamped in a **collet or in a milling chuck**.

Standard:

Bohrfutterkegel **DIN 238**.

Technical description

Taper Ø D	12.065 mm
Plain shank length	40 mm
Drill chuck taper DIN 238	B 12
Shank Ø	10 mm
Type of product	Drill chuck adapter