

Garant
CNMG 120412, Grade: HB7120-1


Order data

Order number	250160 HB7120-1
GTIN	4045197819635
Item class	21G

Description

CNMG 120412 HB7120-1 Grade: HB7120-1
 Chip breaker: VM
 Tolerance: M
 Cutting depth a_p : 0.5 - 4 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Chip breaker	VM
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 4 mm
Cutting conditions	continuous
Corner radius	1.2 mm
Cutting speed v_c main application	80 - 260 m/min

Main application	M
Grade	HB7120-1
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	CNMG 120412
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning